# **FILTER SYSTEMS AND HOLDERS**

## Pyrex<sup>®</sup> Flasks with Hose connection



#### Glass hose to connect a 9 mm inner diameter tubing >Non ground neck to fit

rubber stoppers

# 3 DWK



## **Conical vacuum flask**

>With heavy wall and base > Suitable for use under vacuum

# **DWK**

Cat. No.	Body Ø (mm)	Flask H. (mm)	Capacity (ml)	Max inner neck Ø (mm)	€
232553	73	131	250	18	NC -
232554	89	163	500	23	NC -
232555	111	200	1000	28	NC -
232556	138	248	2000	28	NC -

Cat. No.	Approx. Ø (mm)	Approx. H. (mm)	Capacity (ml)	CN socket	€
232569	90	139	250	24/29	NC -

#### Pyrex<sup>®</sup> Carboys with lateral socket, smooth neck

232560





- ► Complies with ISO 4796
- >29/32 side socket for stopcock
- >Accepts rubber stoppers, thanks to its smooth neck

Cat. No.	Body Ø (mm)	Flask H. (mm)	Capacity (ml)	Max inner neck Ø (mm)	€
232558	181	318	5000	44	NC -


#### Stopcock with ground cone

- For use with flasks with side socket Cat. No. 232558
- ► Model 232559 with Rotaflo® key made of chemically inert PTFE that does not require lubrication

#### Model 232560 with standard glass key

Cat. No.	CN male socket	Total length(mm)	Track (mm)	€
232559	29/32	53	3.0	NC -
232560	29/32	95	4.0	NC -

## DURAN® Borosilicate glass wash bottle



GL 45

NC -

#### 500 ml Borosilicate Glass Storage Flask

Vacuum flask made from Levasintcoated borosilicate glass.

- Protection against breakage and implosion
- ► Volume : 500 ml
- >1 central neck with open cap, 25 mm neck equipped with an analogue pressure gauge
- >2 side necks with GL 18 open caps, equipped with a suction tube, a non-return valve, and a tube with PTFE stopcock

Cat. No.	Description	€
046604	Complete Vacuum safety bottle	NC -

#### **Spare accessories**

Cat. No.	Description	€
046605	Analogue Vacuumeter	NC -
046606	Glass tube with non-return valve	NC -
046607	Bottle 500 ml only	NC -

090377

500